



REQ002X



IK07 IP54

Door station AUDIO 2/1 2-wire stainless steel matt one

Technical characteristics

Architecture

Fixing mode	flush-mounting or surface-mounting
-------------	------------------------------------

Functions

Security functions	privacy function
--------------------	------------------

Compatibility

For labelling strip	12 mm
---------------------	-------

Controls and indicators

Call push-button	call button can be adjusted with light, door release or without function ; call push-button with acknowledge tone (can be switched off) and tactile feedback
Call push-button closing time	max. 3 s
Number of call buttons	2
Operating functions	door release during connection or at any time adjustable

Voltage

Switching voltage door release contact	max. 24 V
--	-----------

Electric current

Switching current door release contact	max. 1 A
--	----------

Dimensions

Depth	25 mm
Insertion depth	22.5 mm
Surface adjustment	17 mm
Dimensions front plate (W x H x D)	133.5 x 242 x 2 mm
Dimensions name plate (W x D)	75.5 x 14.5 mm
Dimensions name plate insert (W x H)	72.4 x 12 mm
Dimensions name plate insert (W x H x D)	72.4 x 12 x 0.14 mm
Height	242 mm
Width of name plate insert	max. 0.5 mm
Width	133.5 mm
Material thickness stainless steel	2 mm

Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material	stainless steel

Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely
LED control	
Operating voltage LED	12 V AC
LED operating current per call push-button module	45 mA
Installation, mounting	
Installation mode	for vertical mounting
Cable	
Conductor Ø	0.5...1.4 mm
Accessories included	
Tool	with opening tool
Equipment	
Door release unlocking time	1...10 s
Front plate	front plate with non-visible opening mechanics and safety rope
Use	
System technology	2-wire
Use conditions	
Operating temperature	-20...55 °C
Storage/transport temperature	-30...80 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Instructions	
Information text	Caution! Do not aim the camera at direct light sources / sunlight, strong contrast or a highly reflective background.