



REQ008X



IK07 IP54

Door station AUDIO 8/1 2-wire stainless steel matt one

Technical characteristics

Architecture

Fixing mode	flush-mounting or surface-mounting
-------------	------------------------------------

Functions

Security functions	privacy function
--------------------	------------------

Compatibility

For labelling strip	12 mm
---------------------	-------

Controls and indicators

Indication / display	device configuration via LED display
----------------------	--------------------------------------

Call push-button	call button can be adjusted with light, door release or without function ; call push-button with acknowledge tone (can be switched off) and tactile feedback
------------------	--

Call push-button closing time	max. 3 s
-------------------------------	----------

Number of call buttons	8
------------------------	---

Operating functions	door release during connection or at any time adjustable
---------------------	--

Voltage

Switching voltage door release contact	max. 24 V
--	-----------

Electric current

Switching current door release contact	max. 1 A
--	----------

Dimensions

Depth	25 mm
-------	-------

Insertion depth	22.5 mm
-----------------	---------

Surface adjustment	17 mm
--------------------	-------

Dimensions front plate (W x H x D)	133.5 x 332 x 2 mm
------------------------------------	--------------------

Dimensions name plate (W x D)	75.5 x 14.5 mm
-------------------------------	----------------

Dimensions name plate insert (W x H)	72.4 x 12 mm
--------------------------------------	--------------

Dimensions name plate insert (W x H x D)	72.4 x 12 x 0.14 mm
--	---------------------

Height	332 mm
--------	--------

Width of name plate insert	max. 0.5 mm
----------------------------	-------------

Width	133.5 mm
-------	----------

Material thickness stainless steel	2 mm
------------------------------------	------

Materials

Colour of design line	Stainless steel
-----------------------	-----------------

Colour	Stainless steel
--------	-----------------

Material	stainless steel
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely
LED control	
Operating voltage LED	12 V AC
LED operating current per call push-button module	45 mA
Installation, mounting	
Installation mode	break-proof flush-mounted call buttons ; installation in surface-mounted or flush-mounted housings ; for vertical mounting
Connection	
Contact	potential-free door release contact
Connection	pluggable connection terminal block with screw terminals
Cable	
Conductor Ø	0.5...1.4 mm
Settings	
Setting	Volume, microphone sensitivity, door release function, camera and call button backlighting adjustable
Accessories included	
Tool	with opening tool
Equipment	
Lighting	durable, homogeneous, white LED call push-button backlighting
Sealing	with joint sealing strip
Brightness	Operating modes name plate backlighting: On, twilight controlled, Off
Cylinder	with error memory
Door release unlocking time	1...10 s
Front plate	front plate with non-visible opening mechanics and safety rope
Use	
System technology	2-wire
Safety	
Protection	Loudspeaker and microphone protected against sabotage
Use conditions	
Operating temperature	-20...55 °C
Storage/transport temperature	-30...80 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Main design line	One

Instructions

Information text

Caution! Do not aim the camera at direct light sources / sunlight, strong contrast or a highly reflective background.