



TRC270D



Plug adaptor radio, ON/OFF, 10/16A, SCHUKO

Technical characteristics

Architecture

Fixing mode pluggable

Functions

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, forced control, status display

Quicklink functions quicklink functions: switching, 2 scenes, time switching, NO contact push-button

Configuration

Number of modules 0

Controls and indicators

Indicator lamp yes

Connectivity

Radio protocol KNX Radio

Receiver category 2

Main electrical features

Frequency 50 Hz

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Number of entry circuits 0

Maximum through current 16 A

Switching current max. 16 A

Dimensions

Depth 77 mm

Assembling height 41 mm

Height 54 mm

Width 98 mm

Frequency

Radio reception frequency 868.3 MHz

Power

Output power 3680 W

Conventional transformers 1600 VA

Electronic transformers and dual-mode transformers	1200 W
--	--------

Materials

Colour of design line	polar white
Surface appearance	matt

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W

Settings

Supported configuration modes	system, PB
-------------------------------	------------

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of outputs	1
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Relative humidity (without condensation)	0...65 % (without condensation)