



TRC301B



Radio Window contact battery-powered, KNX, Quicklink, White

Technical characteristics

Architecture

Fixing mode surface-mounting

Functions

Bus module detachable No

ETS additional functions ETS additional functions: value, delay time, button function, battery condition

Quicklink functions quicklink functions: switching, blind, 2 scenes, time switching, NO contact push-button, forced control

Connectivity

Radio protocol KNX Radio

Receiver category 2

Voltage

Input voltage 3 V

Operating voltage 3 V DC

Electric current

Number of entry circuits 2

Dimensions

Depth of installed product 30 mm

Height of installed product 26 mm

Width of installed product 138 mm

Distance to magnet max. 5 mm

Frequency

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

Power

Radio transmission power < 10 mW

Battery

Battery service life [years] ≈ 4

Materials

Colour polarwhite

RAL colour RAL 9010 - Pure white

Equipment

Number of outputs	0
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver

Use conditions

Operating temperature	0...50 °C
Storage/transport temperature	-25...70 °C