



SF263



## 2 pole Changeover switch 63A I-0-II

### Technical characteristics

#### Architecture

Number of poles 2 P

#### Configuration

Number of modules 4

#### Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

#### Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 4000 V

#### Electric current

Rated current 63 A

Short circuit current withstand with MCB  
63A Curve C - 4,5kA 4.5 kA

Rated operational current in AC21 63 A

#### Dimensions

Depth of installed product 72 mm

Height of installed product 90 mm

Width of installed product 71.5 mm

#### Power

Total power loss under IN 3.6 W

#### Endurance

Electrical durability at nominal load in  
AC21in operating cycles 5000

Number of mechanical operations 100000

#### Installation, mounting

Tightening torque 2,9Nm

#### Connection

Connection cross-sect. flexible conductor 16mm<sup>2</sup>

Connection cross-sect. rigid cable 25mm<sup>2</sup>

Type of contacts changeover with zero position

Type of connection with screw

**Safety**

---

REACH conform	No
RoHS conform	Yes
Halogen free	No

---

**Use conditions**

---

Operating temperature	-20...50 °C
Storage/transport temperature	-40...80 °C

---