




TRM692G



IK04

IP20

Module 1 flush mounted output 3A for shutters or blinds + 2 inputs, KNX radio

Technical characteristics

Architecture

Bus system	KNX
Number of blinds/shutters outputs	1

Functions

Bus module detachable	No
Quicklink functions	quicklink functions: blind, 2 scenes, forced control, up/down push-button

Configuration

Number of modules	0
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Main electrical features

Type of supply voltage	AC
Frequency	50 Hz

Electric current

Number of entry circuits	2
Maximum switching current	3 A

Frequency

Radio reception frequency	868.3 MHz
---------------------------	-----------

Power

Contact rating with 230 V in AC1	690 W
Total power loss under IN	450 mW
Power dissipation per coil	150 mW

Connection

Number of contacts	1
Type of connection	with screw-in lift terminals

Settings

Lamella adjustment on signal duration	< 1 s
---------------------------------------	-------

Equipment

Number of quicklink links	max. 20 transmitter/receiver
Self-retaining for 2 min on signal length	> 1 s
Transmitter duty cycle	1 %
Change-over time for change of direction	< 0.6 s

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-20...70 °C
Relative humidity (without condensation)	0...65 % (without condensation)
