



SF263



2 pole Changeoverswitch 63A I-0-II

Technical characteristics

Architecture

Number of poles	2 P
-----------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated current	63 A
Short circuit current withstand with MCB 63A Curve C - 4,5kA	4.5 kA
Rated operational current in AC21	63 A

Dimensions

Depth of installed product	72 mm
Height of installed product	90 mm
Width of installed product	71.5 mm

Power

Total power loss under IN	3.6 W
---------------------------	-------

Endurance

Electrical durability at nominal load in AC21in operating cycles	5000
Number of mechanical operations	100000

Installation, mounting

Tightening torque	2,9Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²
Type of contacts	changeover with zero position
Type of connection	with screw

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------