



TRM693G



IK04 IP20

quicklink

Module 1 flush mounted output 3A 230V + 2 inputs mains powered, KNX radio

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, 1 up/down button control, push-button, 2 x alarm, status display
Function	reset function (to factory setting) ; Repeat function can be activated to increase the radio range ; easy additional functions: +6 scenes
Light scenes	scene saving lockable ; scene opening via KNX radio appliances
Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control

Configuration

Pre-assembled	confectioned, with 4-core cable
Number of modules	0

Controls and indicators

Indicator lamp	yes
Operation	with manual operation on/off
Control	Activation, for example through switch, push-buttons, timer
Button / push-button	with configuration and function button

Connectivity

Radio protocol	KNX Radio
Receiver category	2
Inputs	with independent, mains supplied, binary input for potential-free contact

Voltage

System supply voltage	230V AC
-----------------------	---------

Electric current

Number of entry circuits	2
Input signal current	33 µA
Maximum through current	3 A
Withstand current in AC1 for the contact path or zone 1	3 A

Dimensions

Height of installed product	40 mm
Dimensions (LLxwwxhh)	40x40x20
Diameter	53 mm
Height	20 mm

Frequency	
Transmission frequency	868 MHz
Radio reception frequency	868.3 MHz
Power	
Total power loss under IN	450 mW
Power dissipation per coil	150 mW
Output power	690 W
Conventional transformers	250 VA
Electronic transformers	250 VA
Radio transmission power	< 10 mW
Measurement	
Input scanning voltage	5 V
Reach distance	
Max. transmission range	30m in house / 100m free field
Materials	
Colour independent of design lines	light grey
Surface appearance	matt
Lighting control	
Fluorescent lamps with electronical ballast (EB)	150 W
- uncompensated	150 W
Fluorescent bulbs control	
Power lighting fluo lamps	150W
Max. power fluo. duo lamp comp. series	150W
Compact fluorescent lamps	150 W
Compact fluorescent lamps	150 W
LED control	
Max number of LED/CFL lamps	20
230V LED lamps	150 W
Power LED	150 W
LED	with transmission status and control LED for On/Off ; with configuration and function LEDs
Incandescent bulbs control	
Max. power with incandescent lamps	500 W
230 V incandescent lamps and halogen lamps	500 W
Installation, mounting	
Installation mode	for installation behind flush-mounted inserts
Connection	
Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 2,5mm ²
Conductor cross-section (flexible)	0.5...1.5 mm ²

Subject to technical modifications

Conductor cross-section (rigid)	0.5...2.5 mm ²
Type of contacts	1NO
Type of connection	with screw-in lift terminals
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
Type of connection	with screw
Cable	
Binary cable length, extendable to	max. 5 m
Binary cable length	≈ 20 cm
Settings	
Supported configuration modes	easy, system, PB, quicklink
Programming	toolless quicklink configuration using buttons and LED display
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	1
Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Modular expandability	No
Transmitter duty cycle	1 %
Use	
Pulse time	min. 50 ms
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...50 °C
Storage/transport temperature	-20...70 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	KNX radio - actuators
Product family	product family: output
Device family	TRM
Main design line	Electronics platform