



TRM702A



Binary 2 inputs device flush mounted battery powered KNX RF

Technical characteristics

Architecture

Bus system Without

Functions

Bus module detachable No

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, 1 up/down button control, push-button, 2 x alarm, status display

Function reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control

Quicklink functions quicklink functions: switching, dimming, blind, 2 scenes, switching time, NO contact push-button, priority, up/down push-button

Configuration

Pre-assembled confectioned, with 4-core cable

Number of modules 0

Controls and indicators

Indicator lamp yes

Control Activation, for example through switches, push-buttons, timers, blind timer switches, magnetic contact

Button / push-button with configuration button

Connectivity

Radio protocol KNX Radio

Receiver category 2

Binary inputs with 2 independent binary inputs for potential-free contacts

Inputs with 2 independent, battery-supplied binary inputs for potential-free contacts

Voltage

Type of voltage input 1 DC

Input voltage 3 V

Electric current

Number of entry circuits 2

Input signal current 33 μ A

Intensity by input 1 mA

Dimensions

Depth of installed product 11 mm

Height of installed product	39 mm
Width of installed product	41 mm
Frequency	
Radio transmission frequency	868.3 MHz
Length	
Max distance to switches	10 mm
Power	
Radio transmission power	< 25 mW
Network configuration	
Network	not dependent on mains power
Measurement	
Input scanning voltage	per channel 5 V
Battery	
Battery service life [years]	≈ 5
Battery / storage battery	with lithium coin cell battery 3 V type: CR 2430
Materials	
Colour independent of design lines	light grey
Material	plastic
Surface appearance	matt
LED control	
LED	with configuration LED
Installation, mounting	
Installation mode	for installation behind flush-mounted inserts
Connection	
Connection cross-sect. flexible conductor	0,5 / 1,5mm ²
Connection cross-sect. rigid cable	0,5 / 1,5mm ²
Connection to	push-button / switch
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
Cable	
Line length	20 cm
Settings	
Programming	toolless quicklink configuration using buttons and LED display
Equipment	
Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Use	
Pulse time	min. 50 ms

Subject to technical modifications

Standards

General standards	EN 300220-2 ; EN 301489-3 ; EN 50491-3 ; EN 60950-1
-------------------	---

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-20...70 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 %

Identification

Application, usage	KNX radio- sensors
Device family	TRM
Main design line	KNX radio/quicklink