



SPB340D

Surge Protection Device 3P T2 TNC Uc 275V In 20kA I_{max} 40kA

Technical characteristics

Configuration

Number of modules 3

Controls and indicators

Indicator lamp Optic

Main electrical features

Rated operational voltage U_e 240 / 415 V

Frequency 50/60 Hz

Nominal discharge current (I_n) 8/20μs, IEC 61643)L-N(PEN)/ N-PE 20 kA

Voltage

Maximum continuous operating voltage U_c 275 V

Voltage protection level U_p according to IEC61643-1 1.35 kV

Voltage protection level U_p L-PE/N-PE according to IEC61643-11 1.5 kV

Voltage level U_p L-N/PEN IEC61643-11 1.35 kV

Electric current

Calibration of the protection upstream 125 A

Max discharge (I_{max}) L-N(PEN)/ N-PE 40 kA

Dimensions

Depth of installed product 58.2 mm

Height of installed product 89.8 mm

Width of installed product 53.4 mm

Electrical specifications

Short-circuit breaking capacity (I_{sc}cr) 25 kA

Network configuration

Network type TN-C

Installation, mounting

Tightening torque 3

Connection

Connection cross-section of input and output with screws, for massive conductors 1.5 / 35 mm²

Connection cross section of access and exit with screws, for flexible conductor 1.5 / 25 mm²

Standards

Approvals	KEMA
Test class IEC61643-11 / VDE0675-6-11	T2

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------
