



SPN440D

SPD 4P pluggable 40kA class 2 with end of life indicator

Technical characteristics

Architecture

Type of pole	3P+N
--------------	------

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Main electrical features

Rated operational voltage U_e	230 / 400 V
Frequency	50/60 Hz
Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	15 kA

Voltage

Maximum continuous operating voltage U_c	275 V
Voltage protection level U_p according to IEC61643-1	1.2 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE	40 kA
--	-------

Dimensions

Width of installed product	72 mm
----------------------------	-------

Power

Total power loss under I_N	0 W
------------------------------	-----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

Use conditions

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C