



TU402



**2-channel remote control**

**Technical characteristics**

**Architecture**

Number of keys 2

**Functions**

ETS additional functions ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Function easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control ; reset function (to factory setting)

Quicklink functions quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Controls and indicators**

Button / push-button with configuration button ; with side locking buttons

**Connectivity**

Radio protocol KNX Radio

AM / FM Modulation FM

Receiver category 2

**Dimensions**

Depth of installed product 15.8 mm

Height of installed product 83 mm

Dimensions (LLxwwxhh) 83 x 46,5 x 15,8 mm

Width of installed product 46.5 mm

**Frequency**

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

**Power**

Radio transmission power < 10 mW

**Reach distance**

Max. transmission range 30m in house / 100m free field

**Battery**

life of battery 5 years

Battery / storage battery with 2 x lithium coin cell battery 3 V type: CR 2430

**LED control**

LED with configuration LED ; with transmission status and battery status LED, red/green/orange

---

**Connection**

Bus connection integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

---

**Equipment**

Number of radio channels 2

---

**Use**

Differentiation characteristic 1 - Sales with labelling field

---

**Safety**

REACH conform No

RoHS conform Yes

Halogen free No

Key with keyring

---

**Use conditions**

Operating temperature -10...45 °C

Energy-saving low intrinsic energy requirement