





TU418



18-channel remote control

Technical characteristics

Functions

ETS additional functions

ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Quicklink functions

quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol

KNX Radio

Receiver category

2

Dimensions

Depth of installed product

16 mm

Height of installed product

133.6 mm

Dimensions (LLxwxhh)

133,6 x 50,2 x 16 mm

Width of installed product

50.2 mm

Frequency

Transmission frequency

868 MHz

Radio transmission frequency

868.3 MHz

Power

Radio transmission power

< 10 mW

Equipment

Number of radio channels

18

Use

Differentiation characteristic 1 - Sales

with labelling field

Safety

Protection index IP

IP30

REACH conform

No

RoHS conform

Yes

Halogen free

No

Use conditions

Operating temperature

0...45 °C