



ST312



Safety transformer 25VA 230V/12-24V

Technical characteristics

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage U_e	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	4000 V
Output voltage 2	24 V
Open circuit voltage secondary	14 / 29 V
Output voltage	12 / 24 V

Electric current

Maximum current of secondary	3 A
Output intensity 2	1.04 A
Output intensity	2.08 A

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	25 VA
Total power loss under IN	1.8 W

Power supply

Transformer	Safety transformer to
-------------	-----------------------

Installation, mounting

Tightening torque	1,2Nm
Suitable for surface mounting	Yes
Suitable for flush-mounting	No
Mounting type	din-Rail

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Cable

Max. cable length to door actuator release	max. 100 m
0.5 A	

Max. cable length to door actuator release 1	max. 50 m
A	

Equipment

On/Off switch	No
---------------	----

Short-circuit protected	Yes
-------------------------	-----

Standards

Standard text	EN 61558-2-6
---------------	--------------

Approvals	EN 61558-2-6
-----------	--------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Temperature protection	Yes
------------------------	-----

Use conditions

Operating temperature	-20...35 °C
-----------------------	-------------

Altitude	<= 2000 m
----------	-----------