



TXA022

Weekly time switch EASY, 2 modules

Technical characteristics

Architecture

Bus system EIB

Functions

Function Functions e.g. switching, dimming, blinds, light scenes, heating, operating modes, date, time

Configuration

Number of modules 2

Controls and indicators

Indication / display LCD display for commissioning

Button / push-button with 5 manual operation buttons

Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

Electric current

Bus consumption 4 mA

Dimensions

Depth of installed product 97 mm

Height of installed product 85 mm

Length 97 mm

Width of installed product 36 mm

Width of rail mounted device (RMD) 2 modules

Power

Total power loss under IN 0.3 W

Dissipated energy in cable 1 W

Battery

Lithium cell power reserve [years] ≈ 5

Materials

RAL colour RAL 7035 - Light grey

Connection

Conductor cross-section (flexible) 1.5...10 mm²

Conductor cross-section (rigid) 1...6 mm²

Bus coupling unit with integral bus coupling unit

Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal
Settings	
Number of program steps	56
Supported configuration modes	system, easy
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Astro program	No
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	2
Number of channels	2
Supply failure reserve	lithium battery
With holidays program	Yes
With random program	Yes
Use	
Cycle	weekly
Differentiation characteristic 1 - Sales	with hinged cover
Differentiation characteristic 2 - Sales	with display
Differentiation characteristic 3 - Sales	with integrated bus coupling unit
Safety	
REACH conform	No
Key	with programming key
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX