



TXA111

IP20

Power supply 30V DC 320 mA

Technical characteristics

Architecture

Bus system EIB

Configuration

Number of modules 4

Connectivity

Bus lines 1

Outputs one output 30 V DC, 320 mA incl. choke

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 30V DC

Output voltage 28...32 V

Filtered output voltage 30V +/- 2V

Electric current

Output current max. 320 mA

Output intensity 320 mA

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Width of rail mounted device (RMD) 4 modules

Power

Total power loss under IN 15 W

Materials

RAL colour RAL 7035 - Light grey

LED control

LED with green LED for display of power supply ; with red LED for display of short-circuit and overload protection per output

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Type of connection	with QuickConnect plug-in terminals
Connection	protected earth conductor must be connected
Type of connection	quick connect

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C