




TGA200



## Power supply 24 V DC 1A

### Technical characteristics

#### Architecture

Bus system EIB

#### Configuration

Number of modules 4

#### Main electrical features

Frequency 50/60 Hz

#### Voltage

Output voltage 24 V DC

Output voltage 24 V

Filtered output voltage 24V +/- 5%

#### Electric current

Output current max. 1 A

Output intensity 1 A

#### Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Width of rail mounted device (RMD) 4 modules

#### Power

Current consumption < 150 mA

Power consumed 16 VA

Power consumption (standby) 0.2 W

Total power loss under IN 15 W

#### Measurement

Voltage measurement range 22.8 to 25.2 V

#### Materials

RAL colour RAL 7035 - Light grey

#### Installation, mounting

Modular version Yes

Suitable for front mounting No

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect

**Equipment**

Short-circuit protected	Yes
-------------------------	-----

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Use conditions**

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C