



TGA200



## Power supply 24 V DC 1A

### Technical characteristics

#### Architecture

Bus system	EIB
------------	-----

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Output voltage	24 V DC
Output voltage	24 V
Filtered output voltage	24V +/- 5%

#### Electric current

Output current	max. 1 A
Output intensity	1 A

#### Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm
Width of rail mounted device (RMD)	4 modules

#### Power

Current consumption	< 150 mA
Power consumed	16 VA
Power consumption (standby)	0.2 W
Total power loss under IN	15 W

#### Measurement

Voltage measurement range	22.8 to 25.2 V
---------------------------	----------------

#### Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

#### Installation, mounting

Modular version	Yes
Suitable for front mounting	No

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of connection	with QuickConnect plug-in terminals
Type of connection	Quickconnect

**Equipment**

Short-circuit protected	Yes
-------------------------	-----

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Use conditions**

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C