



TXA114

IP20

**Power supply 1x 30V DC + 1x 24V DC**

**Technical characteristics**

**Architecture**

Bus system EIB

**Configuration**

Number of modules 4

**Connectivity**

Bus lines 1

Outputs one output 30 V DC, 320 mA incl. choke ; one output 24 V, 640 mA

**Main electrical features**

Frequency 50/60 Hz

**Voltage**

Output voltage 24V+30V

Output voltage 28...32 V

**Electric current**

Output current max. 960 mA

Output intensity 320 mA

**Fuse**

Fuse with electronic short-circuit and overload protection

**Dimensions**

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Width of rail mounted device (RMD) 4 modules

**Power**

Total power loss under IN 4.4 W

**Materials**

RAL colour RAL 7035 - Light grey

**LED control**

LED with green LED for display of power supply per output ; with red LED for display of short-circuit and overload protection per output

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of connection	with QuickConnect plug-in terminals
Connection	protected earth conductor must be connected

**Use**

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C