



TJA470

IK04  **IP20**

Domovea expert

Technical characteristics

Functions

Function	Local and remote connection of the door station with IP end devices, such as smartphone, tablet computer and PC
Function	converting

Configuration

Number of modules	6
-------------------	---

Controls and indicators

With LED indication	Yes
Indication / display	image memory function, protocols visitors for display on Touch indoor station video comfort and IP end devices
Manual selection switches / push-buttons	Selection switch for online/offline mode

Connectivity

Protocol	TCP/IP
Connectors / jacks	with 2 USB sockets type A
Encoding	management of 4 configurable user profiles
IP	Integration of IP cameras into the 2-wire system

Voltage

Operating voltage	24 V DC
Operating voltage	21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3
Operating voltage over bus	21...32 V DC

Electric current

Current consumption (operation)	0.5 A
Making current	650 mA

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Power supply

Operating voltage via power supply	24 V DC
------------------------------------	---------

Connection

Type of connection	with QuickConnect plug-in terminals
Connection	with two RJ45 jacks

Equipment

Demounting protection	No
Radio interface	No
IR interface	No
Updateable	Yes
Visualization	Yes
Web-Server	Yes

Use

System technology	2-wire
-------------------	--------

Software

Update	Software update and downloads via USB interfaces on the device
--------	--

Software	Configuration with Hager Pilot as well as web browser from IE11, Chrome 32, Firefox 27, Edge 20
----------	---

Safety

Degree of contamination	2
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	increased safety management

Use conditions

Operating temperature	-5...45 °C
Altitude	< 2000 m
Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
Relative humidity (without condensation)	85 % at 25 °C