



TJA470

**IK04**  **IP20**

## Domovea expert

### Technical characteristics

#### Functions

Function	Local and remote connection of the door station with IP end devices, such as smartphone, tablet computer and PC
Function	converting

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

With LED indication	Yes
Indication / display	image memory function, protocols visitors for display on Touch indoor station video comfort and IP end devices
Manual selection switches / push-buttons	Selection switch for online/offline mode

#### Connectivity

Protocol	TCP/IP
Connectors / jacks	with 2 USB sockets type A
Encoding	management of 4 configurable user profiles
IP	Integration of IP cameras into the 2-wire system

#### Voltage

Operating voltage	24 V DC
Operating voltage	21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3
Operating voltage over bus	21...32 V DC

#### Electric current

Current consumption (operation)	0.5 A
Making current	650 mA

#### Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

#### Power supply

Operating voltage via power supply	24 V DC
------------------------------------	---------

#### Connection

Type of connection	with QuickConnect plug-in terminals
Connection	with two RJ45 jacks

#### Equipment

Demounting protection	No
Radio interface	No
IR interface	No
Updateable	Yes
Visualization	Yes
Web-Server	Yes

### Use

System technology	2-wire
-------------------	--------

### Software

Update	Software update and downloads via USB interfaces on the device
--------	--

Software	Configuration with Hager Pilot as well as web browser from IE11, Chrome 32, Firefox 27, Edge 20
----------	---

### Safety

Degree of contamination	2
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	increased safety management

### Use conditions

Operating temperature	-5...45 °C
Altitude	< 2000 m
Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
Relative humidity (without condensation)	85 % at 25 °C