



TRB210



## 1 flush mounted dimming output 200W

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Function	reset function (to factory setting)
Light scenes	scene opening via KNX radio appliances, scene saving lockable
Soft startup	bulb-preserving soft startup

#### Configuration

Number of modules	0
-------------------	---

#### Controls and indicators

Indicator lamp	yes
Button / push-button	with configuration and function button

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Main electrical features

Frequency	50 Hz
Rated current	1.3 A

#### Voltage

Operating voltage	230 V AC
-------------------	----------

#### Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

#### Dimensions

Dimensions (Ø x H)	56 x 38 mm
--------------------	------------

#### Frequency

Radio reception frequency	868.3 MHz
---------------------------	-----------

#### Power

Incandescent bulb power	20 / 200 W
Conventional transformers	20...200 VA
Power of the variator	20 / 200 W
Electronic transformers	20...200 W

<b>Endurance</b>	
Transmitter duty cycle	1 %
<b>Materials</b>	
Colour	light grey
<b>LED control</b>	
LED	with configuration and function LEDs
<b>Incandescent bulbs control</b>	
230 V incandescent lamps and halogen lamps	20...200 W
<b>Installation, mounting</b>	
Installation mode	for installation behind flush-mounted inserts
<b>Connection</b>	
Type of load	universal
Type of connection	with screw-in lift terminals
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
<b>Settings</b>	
Programming	toolless quicklink configuration using buttons and LED display
<b>Equipment</b>	
Type of dimmer	universal
Number of quicklink links	max. 20 transmitter/receiver
Bidirectional radio frequency	Yes
Dimming principle	phase cut-on or cut-off according to load type, self-learning
<b>Safety</b>	
Protection index IP	IP30
<b>Use conditions</b>	
Operating temperature	0...45 °C
Energy-saving	low intrinsic energy requirement