



TXA664D



KNX/DALI actuator 4 channels KNX, easy, broadcast

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	REG

Functions

Multi-phase mode	suitable to switch different external conductors
Soft startup	bulb-preserving soft startup

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
Operation	manual operation also possible without bus, e.g. on building site
Manual selection switches / push-buttons	selection switch for manual/bus operation as well as load setting

Main electrical features

Frequency	50/60 Hz
Rated current	185 mA

Voltage

Auxiliary voltage	230 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Power

Power of the variator	3 / 1 W
-----------------------	---------

Materials

Colour	light grey
--------	------------

Connection

Type of load	Universal and LED Retrofit
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings	
Supported configuration modes	system
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	4
Type of dimmer	Dim actuator
Substation input	No
Modular expandability	No
low noise	very low noise
Use	
Local operation/hand operation	Yes
Safety	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX