




TU402



2-channel remote control

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Depth of installed product	15.8 mm
Height of installed product	83 mm
Dimensions (LLxwxhh)	83 x 46,5 x 15,8 mm
Width of installed product	46.5 mm

Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868.3 MHz

Power

Radio transmission power	< 10 mW
--------------------------	---------

Equipment

Number of radio channels	2
--------------------------	---

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

Protection index IP	IP50
---------------------	------

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------