



TYA610A



## Output module 10x 4A /230V~, KNX

### Technical characteristics

#### Architecture

Bus system KNX

#### Functions

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching For switching, e.g. of 10 independent loads or activation of 5 drives

Operating mode any combined operation from drive and switching functions possible

#### Configuration

Number of modules 6

#### Controls and indicators

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

#### Main electrical features

Rated current 4 A

#### Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V

System supply voltage 30V DC via bus

#### Electric current

Bus current consumption (data transfer) 16 mA

Bus current consumption (idle) 8 mA

Number of entry circuits 0

Maximum through current 4 A

Switching current at  $\cos \phi = 0.8$  max. 4 A

#### Dimensions

Depth	65 mm
Width of rail mounted device (RMD)	6 modules
Height	90 mm
<b>Power</b>	
Max. power with electronic transfo.	800 W
Total power loss under IN	0.7 W
Power dissipation per coil	0.15 W
Output power	800 W
Conventional transformers	800 VA
Electronic transformers	800 VA
<b>Lighting control</b>	
Fluorescent lamps with electronical ballast (EB)	12 x 36 W
<b>Fluorescent bulbs control</b>	
Energy-saving lamps	6 x 23 W
Power lighting fluo lamps	6x23W
Max. power fluo. duo lamp comp. series	12 x 36 W
<b>LED control</b>	
Max number of LED/CFL lamps	6
230V LED lamps	6 x 23 W
Power LED	72 W
LED	Status LED integrated in manual operation button
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	800 W
230 V incandescent lamps	800 W
230 V halogen lamps	800 W
230 V incandescent lamps and halogen lamps	800 W
<b>Connection</b>	
Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system
Setting	switching time on change of direction adjustable
<b>Scope of delivery</b>	
Bus connection included	Yes
<b>Equipment</b>	

Subject to technical modifications

Modular expandability

No

---

**Use**

Differentiation characteristic 3 - Sales

with plug-in terminals

---

**Safety**

REACH conform

No

RoHS conform

Yes

Halogen free

No

---

**Use conditions**

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C

---

**Identification**

Main design line

KNX