



TXA116



Power supply 2x 30V DC KNX 640 mA

Technical characteristics

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 4

Connectivity

Bus lines 2

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 28...32 V

Electric current

Output current max. 640 mA

Output intensity 320 mA

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Width of rail mounted device (RMD) 4 modules

Power

Total power loss under IN 3.5 W

Materials

RAL colour RAL 7035 - Light grey

Connection

Conductor cross-section (flexible) 0.75...2.5 mm²

Conductor cross-section (rigid) 0.75...2.5 mm²

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

Protection index IP IP20

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -5...45 °C |
| Storage/transport temperature | -20...70 °C |
