



TXA310

## Binary input 10 fold, 230V~, modular, KNX

### Technical characteristics

#### Architecture

Fixing mode Din-Rail

#### Functions

Bus module detachable No

Easy link functions Switching functions, dimming functions, blind control functions, priority functions, scene functions, heating functions and timer functions

ETS additional functions ETS additional functions: value transmitter 1 and 2 bytes, 2-channel mode, level switch function

#### Configuration

Number of modules 6

#### Controls and indicators

Command by lighting push buttons 10 mA

#### Voltage

Input voltage 230 V

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

Signal voltage 230 V AC

Type of input voltage AC

#### Electric current

Number of entry circuits 10

Intensity by input 34 mA

#### Dimensions

Depth of installed product 60 mm

Height of installed product 90 mm

Length 70 mm

Width of installed product 106 mm

Width of rail mounted device (RMD) 6 modules

#### Length

Max distance to switches 100 mm

#### Power

Total power loss under IN 0.5 W

#### Materials

Colour	stone grey
Material	plastic
<b>Installation, mounting</b>	
Mounting type	din-Rail
<b>Connection</b>	
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Connection to	push-button / switch
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system
<b>Equipment</b>	
Number of outputs	0
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX