



TYB673A



KNX LED Controller 3 Channels constant voltage

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	flush-mounting

Functions

Number of function channels	3
Bus module detachable	No

Configuration

Number of modules	0
-------------------	---

Controls and indicators

Indicator lamp	yes
Button / push-button	with programming button and red programming LED

Main electrical features

Rated current	12 mA
---------------	-------

Voltage

Input voltage	12...24 V DC
Operating voltage over bus	21...32 V DC

Electric current

Bus current consumption (data transfer)	max. 12 mA
Maximum through current	2 A
Output current per channel	max. 2.2 A

Fuse

Fuse	overheating protection (display using LEDs)
------	---

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Incandescent bulbs control

Max. power with incandescent lamps	155 W
------------------------------------	-------

Connection

Conductor cross-section (flexible)	0.75...1.5 mm ²
Conductor cross-section (rigid)	0.75...1.5 mm ²
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals

Bus connection

bus connection via connecting terminal

Cable

Load cable length max. 10 m

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Equipment

Number of outputs 1

Number of inputs 1

Substation input No

Modular expandability No

Interface 1-10 V No

Use

Differentiation characteristic 3 - Sales with screw terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX

Instructions

Special note text

The power supply selected must be compatible with the load connected to the device. ; Caution! Connected loads depend on external LED power supply. Observe manufacturer's data.