




TYB673B



KNX LED Controller 3 Channels constant current

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	flush-mounting

Functions

Number of function channels	3
Bus module detachable	No

Configuration

Number of modules	0
-------------------	---

Controls and indicators

Indicator lamp	yes
Button / push-button	with programming button and red programming LED

Main electrical features

Rated current	12 mA
---------------	-------

Voltage

Input voltage	< 24 V DC
Operating voltage over bus	21...32 V DC

Electric current

Bus current consumption (data transfer)	max. 12 mA
Maximum through current	2 A

Fuse

Fuse	overheating protection (display using LEDs)
------	---

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Incandescent bulbs control

Max. power with incandescent lamps	155 W
------------------------------------	-------

Connection

Conductor cross-section (flexible)	0.75...1.5 mm ²
Conductor cross-section (rigid)	0.75...1.5 mm ²
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal

Cable

Load cable length	max. 10 m
-------------------	-----------

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	1
-------------------	---

Number of inputs	1
------------------	---

Substation input	No
------------------	----

Modular expandability	No
-----------------------	----

Interface 1-10 V	No
------------------	----

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Identification

Main design line	KNX
------------------	-----

Instructions

Special note text	Set direct current supply before connecting supply voltage for the first time with help of DIP-switch ; Caution! Connected loads depend on external LED power supply. Observe manufacturer's data.
-------------------	--