



TYF646T

## 6 Heating output triac 230V flush-mounted

### Technical characteristics

#### Architecture

Bus system EIB

#### Configuration

Number of modules 4

#### Main electrical features

Frequency 50/60 Hz

#### Voltage

System supply voltage 30V DC via bus

#### Electric current

Nominal current per heating output 50 mA

#### Dimensions

Width of installed product 72 mm

#### Power

Power consumed 0.125 W

Total power loss under IN 2 W

#### Materials

RAL colour RAL 7035 - Light grey

#### Installation, mounting

Mounting type din-Rail

#### Connection

Connection cross-sect. flexible conductor 0,5 / 4mm<sup>2</sup>

Connection cross-sect. rigid cable 0,5 / 4mm<sup>2</sup>

Type of connection to the bus TG008 connector

Terminal type of the outputs Cage terminals with screw

#### Equipment

Number of outputs 6

#### Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -25...70 °C