



TXA664D



KNX/DALI actuator 4 channels KNX, easy, broadcast

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	REG

Functions

Multi-phase mode	suitable to switch different external conductors
Soft startup	bulb-preserving soft startup

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
Operation	manual operation also possible without bus, e.g. on building site
Manual selection switches / push-buttons	selection switch for manual/bus operation as well as load setting

Main electrical features

Frequency	50/60 Hz
Rated current	185 mA

Voltage

Auxiliary voltage	230 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Dimensions

Width of rail mounted device (RMD)	6 modules
------------------------------------	-----------

Power

Power of the variator	3 / 1 W
-----------------------	---------

Materials

Colour	light grey
--------	------------

Connection

Type of load	Universal and LED Retrofit
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	4
-------------------	---

Type of dimmer	Dim actuator
----------------	--------------

Substation input	No
------------------	----

Modular expandability	No
-----------------------	----

low noise	very low noise
-----------	----------------

Use

Local operation/hand operation	Yes
--------------------------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Identification

Main design line	KNX
------------------	-----