



TYF646T

6 Heating output triac 230V flush-mounted

Technical characteristics

Architecture

Bus system	EIB
------------	-----

Configuration

Number of modules	4
-------------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

Electric current

Nominal current per heating output	50 mA
------------------------------------	-------

Dimensions

Width of installed product	72 mm
----------------------------	-------

Power

Power consumed	0.125 W
----------------	---------

Total power loss under IN	2 W
---------------------------	-----

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
---	------------------------

Connection cross-sect. rigid cable	0,5 / 4mm ²
------------------------------------	------------------------

Type of connection to the bus	TG008 connector
-------------------------------	-----------------

Terminal type of the outputs	Cage terminals with screw
------------------------------	---------------------------

Equipment

Number of outputs	6
-------------------	---

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C
-------------------------------	-------------