



TYF646T

## 6 Heating output triac 230V flush-mounted

### Technical characteristics

#### Architecture

Bus system	EIB
Fixing mode	Din-Rail

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

System supply voltage	30V DC via bus
-----------------------	----------------

#### Electric current

Nominal current per heating output	50 mA
------------------------------------	-------

#### Dimensions

Width of installed product	72 mm
----------------------------	-------

#### Power

Power consumed	0.125 W
Total power loss under IN	2 W

#### Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	0,5 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	0,5 / 4mm <sup>2</sup>
Type of connection to the bus	TG008 connector
Terminal type of the outputs	Cage terminals with screw

#### Equipment

Number of outputs	6
-------------------	---

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature

-5...45 °C

Storage/transport temperature

-25...70 °C