



TYA610A



Output module 10x 4A /230V~, KNX

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	REG

Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Main electrical features

Rated current	4 A
---------------	-----

Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	16 mA
Bus current consumption (idle)	8 mA
Number of entry circuits	0
Maximum through current	4 A
Switching current at $\cos \varphi = 0.8$	max. 4 A

Dimensions

Depth	65 mm
Width of rail mounted device (RMD)	6 modules
Height	90 mm

Power

Max. power with electronic transfo.	800 W
Total power loss under IN	0.7 W
Power dissipation per coil	0.15 W
Output power	800 W
Conventional transformers	800 VA
Electronic transformers	800 VA

Materials

Colour	light grey
--------	------------

Lighting control

Fluorescent lamps with electronical ballast (EB)	12 x 36 W
--	-----------

Fluorescent bulbs control

Energy-saving lamps	6 x 23 W
Power lighting fluo lamps	6x23W
Max. power fluo. duo lamp comp. series	12 x 36 W

LED control

Max number of LED/CFL lamps	6
Power LED	72 W

Incandescent bulbs control

Max. power with incandescent lamps	800 W
230 V incandescent lamps	800 W
230 V halogen lamps	800 W
230 V incandescent lamps and halogen lamps	800 W

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Modular expandability	No
-----------------------	----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----