



TYFS122



Modular USB KNX Secure Interface

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	REG

Configuration

Number of modules	2
-------------------	---

Compatibility

Compatibility	compatible with USB 1.1/2.0 transmission protocols
---------------	--

Connectivity

Connectors / jacks	with B-type USB socket for data traffic (voltage supply via PC)
--------------------	---

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Width of rail mounted device (RMD)	2 modules
------------------------------------	-----------

Power

Total power loss under IN	0.15 W
Dissipated energy in cable	0.15 W

Storage

Data transmission rate	9.6 kBd
------------------------	---------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey
Material	other

Cable

USB cable length	max. 5 m
------------------	----------

Settings

Supported configuration modes	system
-------------------------------	--------

Equipment

Interface type	USB
----------------	-----

Software

application	bus/PC connection
-------------	-------------------

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Identification

Main design line

KNX