



VE103L

Enclosure,vector,IP5x,3Modules,version Austria

Technical characteristics

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 3

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 93 mm

Internal depth 93 mm

Height of installed product 175 mm

Width of installed product 111 mm

Width in division units 3

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets

2

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Number of openings for flange plates

6

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Safety

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C