



VE212L

Enclosure,vector, JP5x,24Modules,version Austria

Technical characteristics

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 24

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 427 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification od protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets

12

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

2

Quantity of section in width

1

Quantity of rails

2

Can be accessorized

Yes

Number of openings for flange plates

46

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Safety

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C