



WDI101

IP  IP20

## Touch Panel 10" Windows

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

Touch function Yes

#### Connectivity

Connection RJ45 cable in scope of delivery

#### Voltage

Auxiliary voltage 18...36 V DC

#### Dimensions

Assembling height 10 mm

#### Screen

Resolution graphical display 1280 x 800 px

TFT screen size 10 "

Display yes

#### Storage

RAM 4 GB

#### Materials

RAL colour RAL 7016 - Anthracite grey

Material glass

Material family Glass

#### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting

#### Connection

Conductor cross-section (flexible), with wire end sleeve 0.75 mm<sup>2</sup>

#### Settings

Supported configuration modes system

#### Equipment

Text field No

Light intensity 300 cd/m<sup>2</sup>

Processor 2 x 1.75 GHz

**Safety**

---

Protection index IP IP20

**Use conditions**

---

Operating temperature 5...35 °C

Storage/transport temperature -20...60 °C

Relative humidity (without condensation) 10...90 %

**Identification**

---

Composition Control element

Main design line KNX