



VE118L

**Enclosure,vector,IP5x,18Modules,version Austria**

**Technical characteristics**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 18

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 302 mm

Width of installed product 418 mm

Width in division units 18

Thickness of sidewall material 2.5 mm

**Cover, door**

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

**Installation, mounting**

Subject to technical modifications

---

Suitable for outdoor use

No

---

**Connection**

Number of conduit inlets

15

---

**Settings**

Enclosure type

Distributor empty cabinet

---

**Equipment**

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Number of openings for flange plates

46

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

---

**Standards**

GWT Glow wire test

750 °C

European directive WEEE

concerned

---

**Safety**

IK protection code against mechanical impacts

07

Protection class

isol.class II

---

**Use conditions**

Operating temperature

-25...40 °C