



WMPS11

10AX 1 Gang 1 Way Wall Switch

Technical characteristics

Architecture

Number of keys 1

Configuration

Switch mode 1 way

Controls and indicators

Push-buttons No

Main electrical features

Frequency 50/60 Hz

Rated current 10 AX

Dimensions

Depth 24 mm

Insertion depth 12 mm

Height 86 mm

Width 86 mm

Materials

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting

Connection

Conductor cross-section 2 x 4 mm²

Terminal unique patented loop terminal allows neutral looping at the switch

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting without lighting (cannot be illuminated)

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Standard

BS EN 60669-1

Safety

REACH conform

Yes

RoHS conform

Yes

Identification

Appliance switch type

No