



WMPS32

## 10AX 3 Gang 2 Way Wall Switch

### Technical characteristics

#### Configuration

Switch mode	2 way
Antibacterial treatment	No

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Frequency	50/60 Hz
Rated current	10 AX

#### Dimensions

Depth	24 mm
Insertion depth	12 mm
Height	86 mm
Width	86 mm

#### Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white

#### Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting
-------------------	--

#### Connection

Conductor cross-section	2 x 4 mm <sup>2</sup>
Terminal	unique patented loop terminal allows neutral looping at the switch

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

#### Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

#### Standards

Standard	BS EN 60669-1
----------	---------------

#### Identification

Appliance switch type	No
-----------------------	----