



VE318L

Enclosure, vector, IP5x, 54Modules, version Austria

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	54
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	602 mm
Width of installed product	418 mm
Width in division units	18
Thickness of sidewall material	2.5 mm

Cover, door

Type of door closing	Latch
Identification od protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets

15

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

3

Quantity of section in width

1

Quantity of rails

3

Can be accessorized

Yes

Number of openings for flange plates

46

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Safety

IK protection code against mechanical impacts

07

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C