



WMPS42

10AX 4 Gang 2 Way Wall Switch

Technical characteristics

Configuration

Switch mode	2 way
-------------	-------

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Frequency	50/60 Hz
Rated current	10 AX

Dimensions

Depth	24 mm
Insertion depth	12 mm
Height	86 mm
Width	86 mm

Materials

Colour of design line	white
Design lines special colours	white
Colour independent of design lines	white
Colour	white

Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting
-------------------	--

Connection

Conductor cross-section	2 x 4 mm ²
Terminal	unique patented loop terminal allows neutral looping at the switch

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

Standards

Standard	BS EN 60669-1
----------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

