



WDI100

IP  IP20

## Touch Panel 10", Android

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

Touch function Yes

#### Connectivity

Connection RJ45 cable in scope of delivery

Ethernet data rate 10/100 Mbit/s

#### Voltage

Auxiliary voltage 18...48 V DC

Power over Ethernet (PoE) 18...48 V DC

#### Dimensions

Assembling height 10 mm

#### Screen

Resolution graphical display 1280 x 800 px

TFT screen size 10 "

Display yes

#### Storage

RAM 512 MB

#### Materials

RAL colour RAL 7016 - Anthracite grey

Material glass

Material family Glass

#### Installation, mounting

Installation mode for flush-mounted and hollow-wall mounting, for vertical and horizontal mounting

#### Connection

Conductor cross-section (flexible), with wire end sleeve 0.75 mm<sup>2</sup>

#### Settings

Supported configuration modes system

#### Equipment

Text field No

Light intensity	300 cd/m <sup>2</sup>
Processor	1 GHz
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	5...45 °C
Storage/transport temperature	-20...60 °C
Relative humidity (without condensation)	10...90 %
<b>Identification</b>	
Composition	Control element
Main design line	KNX