



WMSS82N

## 2 Gang Double Pole Switched Socket Dual Earth with LED Indicators

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Overvoltage protection	No
------------------------	----

#### Configuration

Number of modules	0
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Rated current	13 A

#### Electric current

Rated current	13 A
---------------	------

#### Dimensions

Depth	29.5 mm
Height	86 mm
Width	146 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Power supply

Special power supply	No special power supply
----------------------	-------------------------

#### Materials

Colour	white
Type of surface treatment	untreated

#### Installation, mounting

Installation mode	for flush-mounted and hollow-wall mounting, for screw fastening
-------------------	---

#### Connection

Type of connection	screw
--------------------	-------

#### Equipment

Number of socket outlets switchable	0
-------------------------------------	---

#### Safety

Protection index IP	IP20
---------------------	------

