



WMGS16PSW

### Technical characteristics

#### Configuration

Switch mode intermediate

#### Controls and indicators

Push-buttons No

#### Main electrical features

Frequency 50/60 Hz

Rated current 20 A

#### Dimensions

Depth 24 mm

Insertion depth 13.1 mm

Height 60 mm

Width 25 mm

#### Materials

Colour silver optics

Material duroplastic

#### Connection

Conductor cross-section 2 x 4 mm<sup>2</sup>

#### Equipment

Lighting without lighting (cannot be illuminated)

#### Safety

REACH conform Yes

RoHS conform Yes

#### Use conditions

Insert insert white

#### Identification

Appliance switch type No