



ADA132T

RCBO Electronic 1M 1P 6kA C-32A 30mA A

Technical properties

Architecture

Type of pole	1P
Curve	C

Electric current

Rated current	32 A
Rated residual operating current I _{dn}	30 mA
Rated current -25°C	40,06 A
Rated current at -20°C	39,39 A
Rated current -15°C	38,72 A
Rated current -10°C	38,03 A
Rated current -5°C	37,33 A
Rated current at 0°C	36,62 A
Rated current 5°C	35,89 A
Rated current 10°C	35,14 A
Rated current 15°C	34,39 A
Rated current at 20°C	33,61 A
Rated current 25°C	32,81 A
Rated current 30°C	32 A
Rated current 35°C	31,16 A
Rated current at 40°C	30,31 A
Rated current at 50°C	28,51 A
Rated current 55°C	27,57 A
Rated current 60°C	26,60 A
Correction factor of rating current for 2 devices placed side by side	1
Correction factor of rating current for 3 devices placed side by side	0,95
Correction factor of rating current for 4 and 5 devices placed side by side	0,90
Correction factor of rating current for 6 devices placed side by side	0,85
Min./max. threshold value of the AC thermal operation	1,13 - 1,45 A

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	6 kA
--	------

Voltage

Rated insulation voltage U _i	250 V
Rated impulse withstand voltage U _{imp}	4000 V
Max. operating voltage	253 V
Rated operational voltage U _e	230 - 240 V
Overvoltage category according to IEC 60947-1	3

Power

Total power loss under I _N	9,63 W
---------------------------------------	--------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Max. Altitude	2000 m
Class of energy limitation I ² t	3
Operating temperature	-5 - 60 °C
Storage/transport temperature	-25 - 60 °C

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	2000

Connection

Cross-section of input with screws, for flexible conductors	1 - 10 mm ²
Cross-section of input with screws, for massive conductors	1 - 16 mm ²

Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	115 mm
Width	17,50 mm
Depth	70 mm

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----