



WMGSDP2N

Technical characteristics

Configuration

Switch mode	2pole
-------------	-------

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Frequency	50/60 Hz
Rated current	20 A

Dimensions

Depth	25 mm
Insertion depth	13.1 mm
Height	59 mm
Width	25 mm

Materials

Colour	white
--------	-------

Equipment

Lighting	with control LED for ON
----------	-------------------------

Use conditions

Insert	insert white
--------	--------------

Identification

Appliance switch type	No
-----------------------	----