



WMPS16

Intermediate Switch

Technical characteristics

Architecture

Number of keys	1
----------------	---

Configuration

Switch mode	intermediate
-------------	--------------

Antibacterial treatment	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Rated current	20 A
---------------	------

Dimensions

Depth	24 mm
-------	-------

Insertion depth	13.1 mm
-----------------	---------

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Materials

Colour of design line	white
-----------------------	-------

Design lines special colours	white
------------------------------	-------

Colour independent of design lines	white
------------------------------------	-------

Colour	white
--------	-------

Connection

Conductor cross-section	2 x 4 mm ²
-------------------------	-----------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Equipment

Lighting	without lighting (cannot be illuminated)
----------	--

Identification

Appliance switch type	No
-----------------------	----