



WMPS22

**10AX 2 Gang 2 Way Wall Switch**

**Technical characteristics**

**Configuration**

Switch mode 2 way

**Controls and indicators**

Push-buttons No

**Main electrical features**

Frequency 50/60 Hz

Rated current 10 AX

**Dimensions**

Depth 24 mm

Insertion depth 12 mm

Height 86 mm

Width 86 mm

**Materials**

Colour of design line white

Design lines special colours white

Colour independent of design lines white

Colour white

**Installation, mounting**

Installation mode for flush-mounted and hollow-wall mounting

**Connection**

Conductor cross-section 2 x 4 mm<sup>2</sup>

Terminal unique patented loop terminal allows neutral looping at the switch

**Scope of delivery**

Component with 2 fixing screws M3.5 x 30 mm

**Equipment**

Lighting without lighting (cannot be illuminated)

**Standards**

Standard BS EN 60669-1

**Safety**

REACH conform Yes

RoHS conform Yes

